

ARRIFLEX D-21



CONFIGURATION OVERVIEW – 1.3.0 / 2011.09

© 2010 Arnold & Richter Cine Technik GmbH & Co. Betriebs KG. All rights reserved. This material is provided "as is" for information purposes only without any warranty. ARRI assumes no responsibility with regard to the performance or use of the products or typographical errors or inaccuracies of given information. Product specifications are subject to change without notice. For a full listing of all available components consult the price list.

Accessories

| | | | | | | | | |
|--|--|--|---|--|---|--|--|---|
| Heated Eyecup HE-4 K2.47794.0, Cable KC42S K2.47771.0 | Auto-Iris Heated Eyecup HE-5 K2.47769.0, Cable KC42S K2.47771.0 | Remote Switch RS-4 K2.46942.0 | WHA-2 Rod Bracket K2.52150.0 | Air-Drying Cartridge K4.70135.0 | Wireless Remote Control WRC-2 incl. Control Knob Unit - for Sets please see Overview 5.5.0 | RS Dovetail Work Light K2.47098.0 (includes Dovetail Handle Mount) | External Display EXD-1, K2.55013.0, (incl. cable KC-100 S 0.8 m / 2.7 ft, K4.65207.0) KC-122 S 20 m / 66 ft, K2.65067.0 | External Sync Unit ESU-1, K2.46006.0 Cables KC-32 & KC-33 and pickup box included |
| 3/8" Accessory Shoe K2.54077.0 | 3/8" Accessory Shoe Expander K2.54030.0 | RS-4 Extension Cable KC40S K2.47207.0 | Update Cable-Set for D-21/435 K4.70174.0 | | | | | |

Basic WRS Components

| | |
|---|--|
| Wireless Main Unit WMU-3 K2.52240.W (White Radio) | Wireless Focus Unit WFU-3 K2.52268.0 |
| Controlled Lens Motor CLM-2 K2.52036.0 | Console CLM-2 K2.52035.0 |
| Wireless Battery Unit WBU-3 K2.52238.0 | Controlled Lens Motor CLM-3, K0.60057.0 |
| Wireless Control Unit WCU-3, K2.65155.W (White Radio) | Wireless Accu Charger WAC-3 K2.52266.0 |

Support, Handles & Extras

| | |
|--|--|
| Bridge Plate BP-8 K2.47090.0 | Low Mode Support Set K2.70004.0 |
| Shoulder Set S-5 complete for D-21/HD, K0.70410.0 incl. | Low Mode Support Set short K2.70010.0 |
| Shoulder Set S-5, K2.70450.0 | Camera Transport Case K2.70000.0 |
| Shoulder Cushion K2.70011.0 | |
| Camera Handgrip Right K2.45886.0 | |

Viewfinder System

| | |
|---|--|
| Wide Angle Eyepiece K2.47081.0 (8x, included in D-21) | Super Wide Angle Eyepiece K2.41822.0 (10x) |
| Finder Extender FE-3 295 mm K2.47082.0 | Finder Extender FE-5 200 mm K2.47304.0 |
| Anamorphic Viewfinder Arm AVF-1 K2.47087.0 | Eyepiece Leveler EL-3 K0.60039.0 |
| Anamorphic Viewfinder Support, K2.70019.0 | |

Storage Solutions

Note:
Storage and signal monitoring solutions can be found in the ARRIFLEX D-21 recommended 3rd party equipment list.

Controller & Radio Modules

| | |
|---|---|
| Functional Expansion Module FEM-2 K2.52226.0 (included in D-21 / D-21 HD) | Universal Radio Module URM-3 K2.52262.W (White Radio) |
|---|---|


Acc. Power / Signal Cable

| |
|---|
| Flash Mag & Sony Fibre Interface Cable Set K2.70410.0 (2x HDTV BNC 0,25 m, 1x 24 V power cable KC45-S) |
| 24-V Power supply cable KC45-S, K4.70104.0 (3-pin to 3-pin) |
| HDTV BNC Cable (HD-SDI) 0,25 m black K2.47840.0, blue K2.47841.0 2 m black K2.47842.0, blue K2.47843.0 10 m black K2.47844.0, blue K2.47845.0 20 m black K2.47838.0, blue K2.47839.0 |

WRS Config. Sample

| | |
|---------------------------------------|---------------------------|
| D-21 incl. URM-3 | CLM-2 or CLM-3 |
| WBU-3, WMU-3, WZU-3, WFU-3 | |

Bodies



ARRIFLEX D-21 K0.70200.0
ARRIFLEX D-21 ANAM K0.70400.0

For Ground Glasses and ARRIGLOW Masks see price list

Monitors

| | |
|---|---|
| 7" HD/SD Monitor HDM-7, incl. power cable, K2.66106.0 needed: Mounting Arm & BNC cable (RG59) | Adapter Hot Shoe 3/8", K2.41102.0 |
| Monitor Arm MMA-65, K2.41101.0 recommended for HDM-7 | Handle Extension Block HEB-1 K4.65107.0 |
| Manfrotto MA484 Mini Ball Head for 3rd party on-board monitors K2.70440.0 | 12V Power Cable for 3rd party onboard monitors KC47-SP-S 11-pin Fischer to 4-pin XLR (Canon), K2.70430.0 |
| Isolating Power Adapter IPA-1 K2.70006.0 (provides 12V isolated from camera ground) | 24 V Plug-on module K2.52001.0 |

Power Supply

| | |
|--|--|
| Power Cable KC-20 K2.41966.0, KC-29 K2.44693.0 (coiled) | Battery VCLX-2 280WH 14.4V/28V, K2.47848.0 |
| 26V power supply NG 12/26 R K2.47351.0 | Charger for ACCU VCLX-2, K2.47849.0 |
| | Cable for charger for ACCU VCLX-2, K2.47850.0 |
| | Transport Case, K2.47847.0 |